

UV LED BULB - 400nm Series

Product Pictures.



Product Applications.

UV light source for photocatalyst.
 UV light source for curing.
 Plan grow light for green house.
 Inspection lighting.
 Architectural lighting.
 Industrial emitters
 Phosphors Stimulation

Product Features.

UV radiation.
 Directly replace for any E27 bulb.
 Superior and unique design for perfect optical performance.
 Up to 50% energy saving than conventional mercury lamps.
 Good thermal management avoids heat degeneration.
 Water-resistant
 Lead-free, mercury-free, environment-friendly.

Typical Technical Characteristics.

General	Light Color	UV Light Source	Beam Angle	Material of Housing
For all types	Ultra Violet	VioLED 400-5R15	15 degree	UV Resistant Polycarbonate.

General	Operating Temperature	Storage Temperature	Dimensions	Remark
For all types	-20 °C ~ +50 °C	-40 °C ~ +80 °C	96*102mm (Dia. * Height)	Custom wavelengths are available.

VioLED International Inc.

4F-2, No.427, Zhongshan N. Rd., Daya Dist., Taichung City 428, Taiwan.
 TEL:886-4-25692507 FAX: 886-4-25691977 <http://www.violed.com.tw>

Specification & Device Selection Guide.


3W UV LED Bulb (Cap Base = E27, Color of Housing = White)

P/N	λ_p	Input Voltage	Power Cons.	Output Power	LED Q'ty	Weight
400-3WUB-230V	395nm ~ 405nm	AC 230V	3.3W	520mw	52pcs	120g
400-3WUB-110V	395nm ~ 405nm	AC 110V	2.9W	520mw	52pcs	120g

7W UV LED Bulb (Cap Base = E27, Color of Housing = White)

P/N	λ_p	Input Voltage	Power Cons.	Output Power	LED Q'ty	Weight
400-7WUB-230V	395nm ~ 405nm	AC 230V	7.5W	1320mw	132pcs	150g
400-7WUB-110V	395nm ~ 405nm	AC 110V	6.4W	1320mw	132pcs	150g


Product Dimensions.



VioLED International Inc.

4F-2, No.427, Zhongshan N. Rd., Daya Dist., Taichung City 428, Taiwan.
TEL:886-4-25692507 FAX: 886-4-25691977 <http://www.violed.com.tw>

Packing Information.



Pieces per Pack = 1 piece
Packs per Outer-Box = 24 (3W)
Packs per Outer-Box = 12 (7W)

Warning.

UV LED light device, radiates intense UV light during operation.
Do not permit children or untrained personnel to operate this device.
Do not look directly into the UV light during operation of the device.
Exposure to UV light, even for a brief period, can damage your eyes.
During operation, the use of Ultra Violet protective goggles is recommended.

Installation.

Way 1: Install in E27 cap base light fixture.



Way 2: Install in E27 cap base connector and plug to power socket.

